



| Region | BRAND                       | Response to Population [RTP] 5<br>Response to Nitrogen [RTN] 5<br>Response to Fungicide [RTF] 5<br>Seeding Vigour<br>Root Strength<br>Drought Tolerance<br>Tonnage Potential<br># Milk/Acre<br>% NDFD<br>% NDF<br>% Starch<br>% Crude Protein<br>TDN |            |      |                           |              |            |               |               |     |       |    |     |     |    |    |    |    |     |     |     |     |     |
|--------|-----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|------|---------------------------|--------------|------------|---------------|---------------|-----|-------|----|-----|-----|----|----|----|----|-----|-----|-----|-----|-----|
|        |                             | Relative Maturity<br>SilageFirst                                                                                                                                                                                                                     | Silage CHU | CHU  | Plant Height<br>Staygreen | Ear Height 1 | Ear Flex 2 | Flower Date 3 | Kernel Rows 4 | 10  | 11    | 12 | 13  | 14  | 15 | 16 | 17 | 18 | 19  | 20  | 21  | 22  |     |
| E      | CP1225VT2P/RIB*             |                                                                                                                                                                                                                                                      | 72         | 1900 | 2025                      | 3            | M-T        | M-H           | SF            | E   | 16-18 | M  | TBD | TBD | 1  | 3  | 3  | 3  | 3   | 3   | 2   | 2   | 3   |
| W      | CP1440VT2P/RIB*             |                                                                                                                                                                                                                                                      | 76         | 1950 | 2100                      | 2            | M-T        | M             | FX            | M-E | 16-18 | M  | M   | M   | 2  | 1  | 2  | 2  | 1   | 2   | 2   | 2   | 2   |
| W      | CP2130VT2P/RIB*             |                                                                                                                                                                                                                                                      | 81         | 2200 | 2350                      | 3            | M-T        | M-H           | SF            | E   | 16-18 | M  | M   | H   | 2  | 2  | 3  | 2  | TBD | TBD | TBD | TBD | TBD |
| W      | CP2288VT2P/RIB*             |                                                                                                                                                                                                                                                      | 82         | 2300 | 2450                      | 3            | M-T        | M-L           | SF            | M   | 16-18 | H  | M   | M   | 2  | 1  | 2  | 2  | 2   | 2   | 2   | 2   | 2   |
| W      | CP2324VT2P/RIB*             |                                                                                                                                                                                                                                                      | 84         | 2350 | 2500                      | 3            | M          | M             | SF            | M   | 16-18 | M  | M   | M   | 2  | 3  | 3  | 2  | 3   | 3   | 3   | 2   | 3   |
| W      | CP2790CONV                  |                                                                                                                                                                                                                                                      | 87         | 2475 | 2625                      | 3            | M-T        | M             | SF            | E   | 16-18 | L  | M   | H   | 1  | 2  | 1  | 2  | 3   | 3   | 3   | 1   | 3   |
| W      | CP2790VT2P/RIB*             |                                                                                                                                                                                                                                                      | 87         | 2500 | 2650                      | 3            | M-T        | M             | SF            | E   | 16-18 | L  | M   | H   | 1  | 2  | 1  | 2  | 3   | 3   | 3   | 1   | 3   |
| W      | CP2732SRR                   | ✓                                                                                                                                                                                                                                                    | 87         | 2650 | 2800                      | 1            | T          | M             | FL            | M   | 16-18 | L  | N/A | N/A | 1  | 2  | 2  | 2  | 2   | 2   | 2   | 3   | 3   |
| E      | CP2965VT2P/RIB*             |                                                                                                                                                                                                                                                      | 89         | 2550 | 2700                      | 3            | M          | M             | SF            | M   | 14-16 | M  | H   | H   | 1  | 2  | 2  | 2  | 2   | 3   | 3   | 3   | 3   |
|        | CP3143VT2P/RIB*             |                                                                                                                                                                                                                                                      | 91         | 2625 | 2775                      | 2            | M-T        | M-H           | SF            | M-L | 18-20 | L  | H   | M   | 2  | 2  | 2  | 2  | TBD | TBD | TBD | TBD | TBD |
| E      | CP3255SSPRO/RIB* <b>NEW</b> |                                                                                                                                                                                                                                                      | 92         | 2650 | 2775                      | 1            | M-T        | M             | SF            | M   | 16-18 | H  | TBD | TBD | 1  | 2  | 3  | 3  | 2   | 2   | 3   | 3   | 2   |
| E      | CP3490VT2P/RIB*             |                                                                                                                                                                                                                                                      | 94         | 2650 | 2800                      | 3            | M-T        | M-H           | SF            | M-L | 18-20 | M  | L   | H   | 1  | 3  | 2  | 1  | 1   | 2   | 3   | 2   | 3   |
| E      | CF956SSS/RIB*               | ✓                                                                                                                                                                                                                                                    | 94         | 2850 | 3000                      | 2            | T          | M             | FL            | M   | 16-18 | L  | N/A | N/A | 2  | 2  | 1  | 2  | 2   | 2   | 3   | 2   | 3   |
| E      | CP3575CONV                  |                                                                                                                                                                                                                                                      | 95         | 2650 | 2800                      | 2            | M          | M             | SF            | M-L | 16-18 | H  | H   | L   | 2  | 2  | 3  | 3  | 3   | 1   | 3   | 3   | 1   |
| E      | CP3575VT2P/RIB*             |                                                                                                                                                                                                                                                      | 95         | 2675 | 2825                      | 2            | M          | M             | SF            | M-L | 16-18 | H  | H   | L   | 2  | 2  | 3  | 3  | 3   | 1   | 3   | 3   | 1   |
| E      | CP3575SS/RIB*               |                                                                                                                                                                                                                                                      | 95         | 2700 | 2850                      | 2            | M          | M             | SF            | M-L | 16-18 | H  | H   | L   | 2  | 2  | 3  | 3  | 3   | 1   | 3   | 3   | 1   |
| E      | CP3720TRE/RIB*              |                                                                                                                                                                                                                                                      | 97         | 2750 | 2900                      | 3            | M          | M             | SF            | E   | 16-18 | M  | H   | M   | 2  | 2  | 2  | 2  | TBD | TBD | TBD | TBD | TBD |
|        | CP3735VT2P/RIB*             |                                                                                                                                                                                                                                                      | 97         | 2750 | 2900                      | 2            | M          | M             | SF            | M   | 16-18 | M  | H   | H   | 1  | 2  | 3  | 2  | 1   | 1   | 3   | 3   | 2   |
| E      | CP3790VT2P/RIB*             |                                                                                                                                                                                                                                                      | 97         | 2775 | 2925                      | 2            | T          | M-H           | SF            | M-L | 16-18 | L  | M   | H   | 2  | 4  | 2  | 1  | 1   | 3   | 4   | 2   | 5   |
| E      | CP3715SSPRO/RIB*            |                                                                                                                                                                                                                                                      | 97         | 2800 | 2950                      | 2            | M-T        | M-H           | SF            | M-E | 18-20 | M  | M   | M   | 2  | 1  | 2  | 3  | 3   | 2   | 1   | 1   | 4   |
| E      | CP3823SS/RIB*               |                                                                                                                                                                                                                                                      | 98         | 2775 | 2925                      | 3            | M-T        | M             | SF            | M   | 16-18 | M  | TBD | TBD | 2  | 2  | 2  | 2  | TBD | TBD | TBD | TBD | TBD |
| E      | CP3980VT2P/RIB*             |                                                                                                                                                                                                                                                      | 99         | 2800 | 2950                      | 3            | M-T        | M-H           | SF            | M   | 14-16 | M  | M   | H   | 2  | 2  | 3  | 3  | 3   | 2   | 2   | 1   | 3   |
| E      | CP4023SRR                   | ✓                                                                                                                                                                                                                                                    | 100        | 3000 | 3150                      | 1            | T          | M             | FL            | M   | 16-18 | L  | N/A | N/A | 3  | 2  | 2  | 1  | 2   | 2   | 2   | 3   | 3   |
|        | CP4188CONV                  |                                                                                                                                                                                                                                                      | 101        | 2800 | 2950                      | 1            | M          | M             | SF            | M   | 16-18 | M  | M   | M   | 1  | 1  | 2  | 1  | 2   | 3   | 2   | 3   | 2   |
| E      | CP4188VT2P/RIB*             |                                                                                                                                                                                                                                                      | 101        | 2850 | 3000                      | 1            | M          | M             | SF            | M   | 16-18 | M  | M   | M   | 1  | 1  | 2  | 1  | 2   | 3   | 2   | 3   | 2   |
|        | CP4188SS/RIB*               |                                                                                                                                                                                                                                                      | 101        | 2875 | 3025                      | 1            | M          | M             | SF            | M   | 16-18 | M  | M   | M   | 1  | 1  | 2  | 1  | 2   | 3   | 2   | 3   | 2   |
| E      | CP4377TRE/RIB*              |                                                                                                                                                                                                                                                      | 103        | 2950 | 3100                      | 3            | M          | M             | SF            | M-E | 16-18 | M  | TBD | TBD | 2  | 3  | 3  | 3  | TBD | TBD | TBD | TBD | TBD |
|        | CP4516TRE/RIB*              |                                                                                                                                                                                                                                                      | 105        | 3000 | 3150                      | 2            | M          | M             | SF            | M-E | 16-18 | M  | M   | H   | 2  | 2  | 3  | 1  | 2   | 5   | 2   | 1   | 4   |
| E      | CP4676SS/RIB*               |                                                                                                                                                                                                                                                      | 106        | 3025 | 3175                      | 1            | M          | M             | SF            | M   | 16-18 | M  | H   | M   | 1  | 3  | 3  | 2  | 2   | 1   | 2   | 3   | 2   |
|        | CP4689PCE RE <b>NEW</b>     |                                                                                                                                                                                                                                                      | 106        | 3100 | 3200                      | 2            | M-T        | M-H           | SF            | L   | 16-18 | M  | H   | M   | 2  | 2  | 1  | 2  | 2   | 2   | 3   | 2   | 2   |
| E      | CP4757VT2P/RIB*             |                                                                                                                                                                                                                                                      | 107        | 3050 | 3200                      | 3            | M-T        | M-H           | SF            | M   | 18-20 | M  | M   | M   | 3  | 1  | 2  | 1  | 1   | 3   | 3   | 3   | 1   |

## KEY

## Scale

- 1 = Excellent  
2 = Above average  
3 = Average  
4 = Below average  
5 = Fair

Product descriptions and ratings are generated from Answer Plot trials and/or from the genetics supplier and may change as additional data is gathered.

## 1 Plant Height

- T = Tall  
M = Medium  
S = Short

## 2 Ear Height

- H = High  
M = Medium  
L = Low

## 3 Ear Flex

- FL = Flex  
SF = Semi-flex  
FX = Fixed

## 4 Flower Date

- L = Late  
M = Medium  
E = Early

## 5 RTP/RTN/RTF Ratings

- L = Low response  
M = Moderate response  
H = High response  
TBD = To be tested in 2027.



\*Before opening a bag of seed, be sure to read, understand and accept the stewardship requirements, including applicable refuge requirements for

insect resistance management, for the biotechnology traits expressed in the seed as set forth in the Bayer Technology Stewardship Agreement that you sign. By opening and using a bag of seed, you are reaffirming your obligation to comply with the most recent stewardship requirements.

W = Western Hybrid | E = Eastern Hybrid